

# Spray Washers

We can offer top loading single stage spray washing machines. Cleaning parts prior to maintenance or between production phases is often necessary, not only for technical reasons, but also for operator comfort. The Spintec wash machine is the ideal solution for cleaning parts quickly and in a closed chamber for a better working environment.



- Cleans parts fast and efficiently
- Easy to control with digital operating timer and temperature control
- Durable materials: stainless steel chamber, spray pipes, nozzles, pump and valves
- Safe and ergonomic working environment: lid with gas springs, safety switch and exhaust connections
- Level controller protects functions from dry running
- Air gun for drying of the parts and adjustable feet for easy installation, standard in all machines

## Options

- Loading trolley for ergonomically moving heavier loads
- Removable basket gives more possibilities for material handling in production
- 7-day timer heats the liquid up according to the operation schedules
- Closed loop filtration cleans the wash liquid particle free and prolongs wash liquid lifespan time
- Oil separator removes free oil from wash liquid and reduces waste liquid volumes
- Automatic refill and detergent dosing ensure consistent cleaning result for longer production series
- Heat insulation saves energy in cooler environments

Name	Spintec 60	Spintec 82	Spintec 105	Spintec 125	
Body Diameter (mm)	600	820	1050	1250	
Load max (kg)	80	150	200	300	
Load height max. fixed basket (mm)	300	400	500	640	
Load height max. removable basket (mm)	-	360	460	600	
Container volume (l)	50	120	220	450	
External Dimensions	Width	755	950	1250	
	Length	1000	1250	1500	
	Height (lid closed)	1150	1250	1350	1600
	Height (lid open)	1550	1750	2000	2400
Pump capacity (l/min)	60	120	140	190	
Pump pressure (Bar)	1.5	2	3	3.2	
Heating (kW)	4	4	7.5	15	

## Recommended Non-foaming Cleaning Fluids for Spintec Spray Washer

Type	Package Size	Product Code	Alkaline or Acid	PH approx	Dilution % Suggested	Temp °C Suggested	Suggested Use	Comments
Decoclean 440	25 Litre	362945	Alkaline	13	5 - 15%	50 - 80°C	Heavy contamination on Ferrous metals only	Do not use on Non-ferrous metals. Rinse well.
Decospray TM	25 Litre	363162	Alkaline	9.6	1 - 3%	60 - 70°C	Removes oils and does not attack metals	It temporarily protects the parts against oxidation
Decospray HT13	25 Litre	363163	Alkaline	14	2 - 3%	70 - 75°C	Removes oils from Non-ferrous materials	Very high degreasing power